SFG22HD-14-B



G22HD High Capacity Sector Frame with 2 7/8in OD x 14.5ft face. Base Kit Only. No antenna pipes.

Product Classification

Product Type Product Series High capacity Tower sector frame

General Specifications

Application	4G LTE antenna/radio mount
Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	0
Sectors, quantity	1
Tower Taper	Non-tapered Tapered
Dimensions	
Face Width	4.42 m 14.5 ft
Width	4,419.6 mm 174 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	38.1 mm 1.5 in
Stand-off Distance	1,041.4 mm 41 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222-G

Packaging and Weights

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

SFG22HD-14-B

Included

Frame | Stiff arms (2) | Tower attachment

Packaging quantity

Regulatory Compliance/Certifications

Classification

Above maximum concentration value

ROHS

Agency

Compliant/Exempted

Compliant/Exempted

1

UK-ROHS

CHINA-ROHS

50

* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025