SFG23RHDX-10-3-96



G23RHDX Tower Sector Frame with spine extension for RRU Mounting, $10.5 \, \text{ft} \times 2.88 \, \text{in} \, \text{OD} \, \text{face pipes, includes three} \, 2.88 \, \text{OD} \times 96 \, \text{in antenna pipes}$

- Extended spine for SFG23 RHDX mounts that decrease PIM from radio relocation
- Increased versatility and stability
- Updated frame provides higher loading
- More RRU mounting available, reducing need for additional mounts
- · Better load management
- · Less structure stress
- · Can be used in combination with APEX RRU mounts

Product Classification

Product Type High capacity Tower sector frame

Product Brand PIM-guard

Product Series G2

General Specifications

Application 4G LTE antenna/radio mount

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Patent Number Patent pending

Pipe, quantity 3
Sectors, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Pipe Length 2,438.4 mm | 96 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 218.44 mm | 8.6 in

Mounting Diameter, minimum 38.1 mm | 1.5 in



SFG23RHDX-10-3-96

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Antenna mounting pipes | Crossover plates | Frame | Stiff arms (2) | Tower attachment

Packaging quantity 1

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code