
# 810010276/DB | D-288-LA-8W-M12NS



Fiber OSP cable, LightScope® ZWP Single Jacket/Single Armor, 288 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

• Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	D-LA
General Specifications	
Armor Type	Corrugated steel
Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-free
Jacket Color	Black
Jacket Marking	Meters
Subunit, quantity	24
Fibers per Subunit, quantity	12
Total Fiber Count	288
Dimensions	
Buffer Tube/Subunit Diameter	2.5 mm   0.098 in
Diameter Over Jacket	19.6 mm   0.772 in

# Representative Image


Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



# 810010276/DB | D-288-LA-8W-M12NS

MDPE Outer Jacket Steel Tape Armoring Binder Ripcord (2) Water Swellable Tape Binder 2.5mm Gel-Free Buffer Tubes 250 micron Fibers Dielectric Strength Member



## Material Specifications

Jacket Material	PE
Mechanical Specifications	
Minimum Bend Radius, loaded	294 mm   11.575 in
Minimum Bend Radius, unloaded	196 mm   7.717 in
Tensile Load, long term, maximum	800 N   179.847 lbf
Tensile Load, short term, maximum	2700 N   606.984 lbf
Compression	44 N/mm   251.246 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	6.62 N-m   58.592 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	304 m   997.375 ft
Optical Specifications	

### **Optical Specifications**

Fiber Type

G.652.D and G.657.A1 | G.652.D and G.657.A1

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



# 810010276/DB | D-288-LA-8W-M12NS

# **Environmental Specifications**

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)	
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)	
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)	
Cable Qualification Standards	ANSI/ICEA S-87-640   EN 187105   Telcordia GR-20	
Environmental Space	Aerial, lashed   Buried	
Jacket UV Resistance	UV stabilized	
Water Penetration	24 h	
Water Penetration Qualification Method	ANSI/ICEA S-87-640	
Water Penetration Test Method	FOTP-82   IEC 60794-1 F5	

#### **Environmental Test Specifications**

Cable Freeze	-2 °C   28.4 °F
Cable Freeze Test Method	FOTP-98   IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

#### Cable weight

269 kg/km | 180.76 lb/kft

### Regulatory Compliance/Certifications

#### Agency

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

DB-8W-LT – LightScope® ZWP Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

**COMMSCOPE**<sup>®</sup>

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025