

Fiber indoor/Outdoor cable, OFNR/LSZH Riser Rollable Ribbon Dual Rated Backbone, 48 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Cca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series N-MP

General Specifications

Cable Type Riser rated low smoke

Construction Type Non-armored

Subunit Type Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet


Total Fiber Count 48

Dimensions

Diameter Over Jacket 6.6 mm | 0.26 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded 132 mm | 5.197 in

Minimum Bend Radius, unloaded53 mm | 2.087 inTensile Load, long term, maximum396 N | 89.024 lbf

Tensile Load, short term, maximum 1320 N | 296.748 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Page 2 of 6



Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Rating\$1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR (UL) and c(UL)

Flame Test Method FT4 | UL 1666

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -10 °C to +60 °C (+14 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 44.9 kg/km | 30.171 lb/kft

Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8G1-RR-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Rollable Ribbon Fiber (ITU-T G.657.A2, B2)

Page 3 of 6

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

CS-8G1-RR-MP

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Rollable Ribbon Fiber (ITU-T G.657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.3 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** $249 \, \mu m$ **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum 0.5 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 1 turn
 0.50 dB @ 1,550 nm
 1 0.00 dB @ 1,625 nm

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.10 dB @ 1,550 nm
 0.20 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.03 dB @ 1,550 nm
 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G1-RR-MP

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.30 dB/km @ 1,550 nm | 0.40 dB/km @ 1,310 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

Mode Field Diameter 8.6 μ m @ 1,310 nm | 9.8 μ m @ 1,550 nm

Mode Field Diameter Tolerance $\pm 0.4 \,\mu\text{m}$ @ 1310 nm | $\pm 0.5 \,\mu\text{m}$ @ 1550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

