

Fiber outdoor drop cable, LightScope ZWP® Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.Al, 2 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 5000 ft

 \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®
Product Type Fiber drop cable

**Product Series** O-DF

Government Funding Build America Buy America (BABA) compliant\*

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

**Subunit Type** Gel-filled

Jacket Color Black

Jacket Marking Feet

Subunit, quantity 1

Fibers per Subunit, quantity 2

Total Fiber Count 2

**Dimensions** 

**Height Over Jacket** 4.5 mm | 0.177 in


**Cable Length** 1,524 m | 5000 ft

**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 7.9 mm | 0.311 in



## Representative Image



#### Material Specifications

Jacket Material PE

#### Mechanical Specifications

Minimum Bend Radius, loaded86 mm | 3.386 inMinimum Bend Radius, unloaded81 mm | 3.189 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1334 N | 299.895 lbfCompression10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 35 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 1047 m | 3,435.039 ft

COMMSC PE°

## **Optical Specifications**

**Fiber Type** G.652.D and G.657.A1 | G.652.D and G.657.A1

## **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+75 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+167 \,^{\circ}\text{F}$ )

Cable Qualification StandardsANSI/ICEA S-110-717

Environmental Space Aerial, self-support | Buried

Jacket UV Resistance UV stabilized

Water Penentration 24 h

Water Penentration Test Method FOTP-82 | IEC 60794-1 F5

#### **Environmental Test Specifications**

**Cable Freeze** -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

## Packaging and Weights

Cable weight 39 kg/km | 26.207 lb/kft

#### Included Products

DB-8W-LT – LightScope ZWP® Singlemode Fiber

#### \* Footnotes

**COMMSCOPE®** 

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable