

Fiber outdoor drop cable, LightScope® ZWP Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.A1, 12 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 5000 ft

• \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	0-DF
Government Requirements	Build America Buy America (BABA) compliant*
General Specifications	
Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Feet
Location of Manufacturing	Catawba, North Carolina
Subunit, quantity	1
Fibers per Subunit, quantity	12
Total Fiber Count	12
Dimensions	
Height Over Jacket	4.5 mm   0.177 in
Cable Length	1,524 m   5000 ft
Buffer Tube/Subunit Diameter	3 mm   0.118 in

Page 1 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2025




ΡE

**Diameter Over Jacket** 

7.9 mm | 0.311 in

#### Representative Image



#### Material Specifications

Jacket Material

Mechanical Specifications

Minimum Bend Radius, loaded	86 mm   3.386 in	
Minimum Bend Radius, unloaded	81 mm   3.189 in	
Tensile Load, long term, maximum	400 N   89.924 lbf	
Tensile Load, short term, maximum	1334 N   299.895 lbf	
Compression	10 N/mm   57.101 lb/in	
Compression Test Method	FOTP-41   IEC 60794-1 E3	
Flex	35 cycles	
Flex Test Method	FOTP-104   IEC 60794-1 E6	
Impact	2.94 N-m   26.021 in lb	
Impact Test Method	FOTP-25   IEC 60794-1 E4	
Strain	See long and short term tensile loads	
Strain Test Method	FOTP-33   IEC 60794-1 E1	
Twist	10 cycles	
Twist Test Method	FOTP-85   IEC 60794-1 E7	

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2025



**COMMSCOPE**<sup>®</sup>

Page 2 of 7

#### Vertical Rise, maximum

1047 m | 3,435.039 ft

#### **Optical Specifications**

Fiber Type

G.652.D and G.657.A1 | G.652.D and G.657.A1

#### **Environmental Specifications**

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-110-717   Telcordia GR-20
Environmental Space	Aerial, self-support   Buried
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82   IEC 60794-1 F5

#### Environmental Test Specifications

Cable Freeze	-2 °C   28.4 °F	
Cable Freeze Test Method	FOTP-98   IEC 60794-1 F15	
Drip	70°C   158°F	
Drip Test Method	FOTP-81   IEC 60794-1 E14	
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)	
Heat Age Test Method	IEC 60794-1 F9	
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)	
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11	
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)	
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1	

#### Packaging and Weights

**Cable weight** 

39 kg/km | 26.207 lb/kft

#### Included Products

DB-8W-LT – LightScope® ZWP Singlemode Fiber

Page 3 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2025



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 4 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 10, 2025



#### LightScope® ZWP Singlemode Fiber

### LightScope<sup>®</sup> 2000

#### Product Classification

Portfolio	CommScope®	
Product Type	Optical fiber	
General Specifications		
Cladding Diameter	125 µm	
Cladding Diameter Tolerance	±0.7 μm	
Cladding Non-Circularity, maximum	0.7 %	
Coating Diameter (Colored)	249 µm	
Coating Diameter (Uncolored)	242 µm	
Coating Diameter Tolerance (Colored)	±13 μm	
Coating Diameter Tolerance (Uncolored)	±5 μm	
Coating/Cladding Concentricity Error, maximum	12 µm	
Core Diameter	8.3 µm	
Core/Clad Offset, maximum	0.5 µm	
Proof Test	689.476 N/mm <sup>2</sup>   100000 psi	
Dimensions		
Fiber Curl, minimum	4 m   13.123 ft	
Mechanical Specifications		
Macrobending, 20 mm Ø mandrel, 1 turn	0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm	
Macrobending, 30 mm Ø mandrel, 10 turns	0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm	
Macrobending, 60 mm Ø mandrel, 100 turns	0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm	
Coating Strip Force, maximum	8.9 N   2.001 lbf	
Coating Strip Force, minimum	1.3 N   0.292 lbf	
Dynamic Fatigue Parameter, minimum	20	

Page 5 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 22, 2024



### DB-8W-LT

### Optical Specifications

Cabled Cutoff Wavelength, maximum	1260 nm
Point Defects, maximum	0.1 dB
Zero Dispersion Slope, maximum	0.092 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1324 nm
Zero Dispersion Wavelength, minimum	1300 nm
Optical Specifications, Wavelength Specific	
Attenuation, maximum	0.22 dB/km @ 1,550 nm ( 0.25 dB/km @ 1,490 nm ( 0.25 dB/km @ 1,625 nm ( 0.36 dB/km @ 1,310 nm ( 0.36 dB/km @ 1,385 nm
Attenuation, typical	0.19 dB/km @ 1,550 nm   0.33 dB/km @ 1,310 nm
Backscatter Coefficient	-79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm
Dispersion, maximum	18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
Index of Refraction	1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm
Mode Field Diameter	10.4 μm @ 1,550 nm   9.2 μm @ 1,310 nm   9.6 μm @ 1,385 nm
Mode Field Diameter Tolerance	±0.4 μm @ 1310 nm   ±0.5 μm @ 1550 nm   ±0.6 μm @ 1385 nm
Polarization Mode Dispersion Link Design Value, maximum	0.04 ps/sqrt(km)
Standards Compliance	ITU-T G.652.D   ITU-T G.657.A1

#### Environmental Specifications

Heat Aging, maximum	0.05 dB/km @ 85 °C
Temperature Dependence, maximum	0.05 dB/km
Temperature Humidity Cycling, maximum	0.05 dB/km
Water Immersion, maximum	0.05 dB/km @ 23 °C

#### Regulatory Compliance/Certifications

Classification

#### Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

#### \* Footnotes

Page 6 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 22, 2024



### DB-8W-LT

Temperature Dependence, maximumTemperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)Temperature Humidity Cycling, maximumTemperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

Page 7 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 22, 2024

