


# 810010256/50 | O-024-DF-HY-F24NS/30G /8W024/1X24AWG (5K)



LightScope ZWP® Fiber + Tone Wire Outdoor Drop Cable, 1–24 fiber  
Arid Core construction, central loose tube, 5000 ft

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable, fiber and tone-wire
<b>Product Brand</b>	LightScope ZWP®
<b>Government Funding</b>	Build America Buy America (BABA) compliant*

## General Specifications


<b>Cable Type</b>	Central loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	24
<b>Tone Wire, quantity</b>	1
<b>Total Fiber Count</b>	24

## Dimensions

<b>Height Over Jacket</b>	0.18 in   4.572 mm
<b>Cable Length</b>	5000 ft   1,524 m
<b>Buffer Tube/Subunit Diameter</b>	0.12 in   3.048 mm
<b>Diameter Over Jacket</b>	0.39 in   9.906 mm
<b>Diameter Over Messenger Jacket</b>	0.08 in   2.032 mm
<b>Tone Wire Gauge</b>	24 AWG

# 810010256/50 | O-024-DF-HY-F24NS/30G /8W024/1X24AWG (5K)

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	3.4 in   86.36 mm
<b>Minimum Bend Radius, unloaded</b>	2.5 in   63.5 mm
<b>Tensile Load, long term, maximum</b>	90 lbf   400.34 N
<b>Tensile Load, short term, maximum</b>	300 lbf   1,334.466 N
<b>Compression</b>	57 lb/in   1.018 kg/mm
<b>Compression Test Method</b>	FOTP-41   IEC 60794-1 E3
<b>Flex</b>	35 cycles
<b>Flex Test Method</b>	FOTP-104   IEC 60794-1 E6
<b>Impact</b>	2.17 ft lb   2.942 N-m
<b>Impact Test Method</b>	FOTP-25   IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	FOTP-33   IEC 60794-1 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	FOTP-85   IEC 60794-1 E7
<b>Vertical Rise, maximum</b>	2917 ft   889.102 m

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1   G.652.D and G.657.A1
-------------------	---

# 810010256/50 | O-024-DF-HY-F24NS/30G /8W024/1X24AWG (5K)

---

## Environmental Specifications

<b>Installation temperature</b>	-30 °C to +70 °C (-22 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Cable Qualification Standards</b>	ANSI/ICEA S-110-717
<b>Environmental Space</b>	Aerial, lashed   Buried
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	FOTP-82   IEC 60794-1 F5

## Environmental Test Specifications

<b>Cable Freeze</b>	-2 °C   28.4 °F
<b>Cable Freeze Test Method</b>	FOTP-98   IEC 60794-1 F15
<b>Drip</b>	70 °C   158 °F
<b>Drip Test Method</b>	FOTP-81   IEC 60794-1 E14
<b>Heat Age</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Heat Age Test Method</b>	IEC 60794-1 F9
<b>Low High Bend</b>	-30 °C to +60 °C (-22 °F to +140 °F)
<b>Low High Bend Test Method</b>	FOTP-37   IEC 60794-1 E11
<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

<b>Cable weight</b>	27.147 lb/kft   40.399 kg/km
---------------------	------------------------------

## Included Products

DB-8W-LT – LightScope ZWP® Singlemode  
Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable