SRC9-U5A1F1BP000



NOVUX[™] Specialty Range Closure 10, splice only, no adapters, no splitters, 4 splices, SMOUV® 45mm splice protectors, black, tie-wraps & silicon tape (Cable range: 2 - 6.2mm)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Product Classification

Regional Availability	Asia EMEA Latin America North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC10
General Specifications	
Cable Capacity, Drop	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 2 Round 2-6.2 mm (0.08-0.24 in)
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	In-line
Color	Black
Mounting	Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included
Network Area Type	Drop
Port, quantity	2
Splice Tray Included, quantity	1
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, maximum	4

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 23, 2025



SRC9-U5A1F1BP000

Splicing Capacity, Single	Fusion, maximum	4
Splicing Type, Supported		Single fusion
Splitter Type		No splitter
Dimensions		
Width		76 mm 2.992 in
Depth		26 mm 1.024 in
Length		210 mm 8.268 in
Cable Entry Drop Port Dia	meter	6 mm (0.24 in) mm
Material Specifications		
Material Type		Impact-resistant polymer
Optical Specifications		
Fiber Type		G.657.A1 G.657.A2 G.657.B3
Environmental Specifications		
Operating Temperature		-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space		Above ground Below ground Direct burial
Qualification Standards		IEC 60529, IP68 + 1 m waterhead IEC 61753-1, category G
UV Resistance		UV stabilized
Packaging and Weights		
Packaging quantity		1
Packaging Type		Box Carton
Weight, net		0.157 kg 0.346 lb
Regulatory Compliance/Certifications		
Agency	Classification	
CHINA-ROHS	Above maximum concentrat	ion value
ROHS	Compliant/Exempted	

UK-ROHS Compliant/Exempted



Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 23, 2025

