

SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

Product Classification

| | |
|----------------------|---|
| Product Type | Adapter |
| Product Brand | SnapStak® |
| Ordering Note | CommScope® standard product in the United States and Canada |

General Specifications

| | |
|--------------------|---------------------|
| Accessories | Adapters |
| Color | Black |
| Mounting | 3/4 in through hole |

Dimensions

| | |
|---------------|-------------------|
| Height | 76.2 mm 3 in |
| Width | 25.4 mm 1 in |
| Length | 6.35 mm 0.25 in |

Material Specifications

| | |
|----------------------|--------------------|
| Material Type | Engineered plastic |
|----------------------|--------------------|

Mechanical Specifications

| | |
|---------------------------|---|
| Maximum Loading | Quadruple stack for SSH-M Triple stack for hangers SSH-XL, SSH-L Triple stack, 1-5/8 in cable |
| Vibration Survival | ≥4 hours at resonant frequency |

Environmental Specifications

| | |
|---|---|
| Operating Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |
| UV Resistance, minimum with no degradation | ≥1000 hours exposure in accelerated UV life chamber |

Packaging and Weights

SSHR-10

| | |
|---------------------------|--------------------|
| Height, packed | 17 cm 6.693 in |
| Width, packed | 13 cm 5.118 in |
| Length, packed | 10 cm 3.937 in |
| Packaging quantity | 10 |
| Weight, gross | 0.15 kg 0.331 lb |