

MC-KD10M-B



Heavy Duty Double T-Arm Monopole Mount Base Kit, Includes (2) Ring Mounts for 15"-50" OD Monopole, 10.5 ft x 3-1/2" OD face pipes. Antenna Pipes not included.

Heavy Duty Double T-Arm mount design for Monopole applications featuring sturdy corner tie-backs for added stability. Includes 3-1/2" OD face pipes. Antenna Pipes not included.

Product Classification

Product Type Monopole T-frame kit

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity 0
Sectors, quantity 3

Dimensions

Face Width 3.2 m | 10.5 ft
Width 3,048 mm | 120 in
Mounting Diameter, maximum 1270 mm | 50 in
Mounting Diameter, minimum 381 mm | 15 in
Stand-off Distance 1,244.6 mm | 49 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative
Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Ring mounts (2) | Stand-off arms
Packaging quantity 1
Weight, net 684.067 kg | 1,508.11 lb

MC-KD10M-B

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--