

SHK-SERIES-HANGER-BLOCKS

Base Product



SHK-Series Hanger Kits

Product Classification

Product Type

Hanger kit

Product Brand

ValuSite™

General Specifications

Color

Black

Hanger Type

Composite clamp

Mounting

M8 hardware

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

UV Resistance, minimum with no degradation

≥100 hours exposure in accelerated UV life chamber