			4			3			
D	1.2 FOR PA 2.0 DESIGN NO 2.1 ANY HA IDENTIF REQUIR TEMPOI PRESEF 3.0 MANUFACT 3.1 TIGHTE TURN-C THE U-E 4.0 TEST 5.0 PACKAGING 5.1 PACKAG	ETRIC DIMENSION TENT INFO: https TES AZARDS OR OBS FIED PRIOR TO IN RED TO MAINTAIN RARY AND/OR PE RVE THE CLIMBIN URING/SPECIAL I SN ALL BOLTS SE DF-NUT METHOD BOLT. GING SHALL MEE D DOCUMENT TO	NS ARE IN BRACKETS [X. X] <u>s://www.cs-pat.com</u> TRUCTIONS TO THE CLIMBING FACILITY AND ISTALLING THE APPURTENANCE. ADDITIONA IN THE INTEGRITY OF THE SAFETY CLIMB. DU ERMANENT PRECAUTIONARY MEASURES SH NG FACILITY AND/OR SAFETY CLIMB. REQUIREMENTS CURING FLAT PLATES BY THE TURN-OF-NUT WITH ATTENTION TO LEAVE EQUAL DISTANC ET COMMSCOPE REQUIREMENTS PER DOCU D BE PLACED INSIDE POLYBAG AND THEN IN 'BE SUPPLIED, BAGGED AND SHIPPED	AL PRODUCTS IRING INSTAL IOULD BE TA I METHOD. T CE AND EQU/	S MAY BE LATION, KEN TO IGHTEN ALL U- AL FORCE ON B 3005			A	
С			ANGLE MEM	BER	\sum		JETAIL A SCALE 1:3		
- >	5		SET-UP	DLIN					
В					- 5		4 DETAIL SCALE		-(1)
			ROUND MEN SET-UP MBERS PROVIDED FOR ASSEMBL ITS MAY BE SHIPPED AS PARTS V DESCRIPTION 20' ANGLE SIDE RAIL	Y PURPOS	•	KIT. NOTE NO.			
A	2	CL06R.01	20" LADDER RUNG	6	1.69 LBS				
	3 4	HKCLU.02 GB-03145	BACKING PLATE 3/8" X 1-1/2" GALV BOLT KIT	6 16	0.95 LBS 0.07 LBS				
	5	GB-03145 GJB0380	8" GALV J-BOLT KIT	8	0.07 LBS 0.23 LBS				SUF
	6	GWF-03	3/8" GALV FLAT WASHER	12	0.01 LBS				50F
	7	CWI 03		0	0.01189				

0.01 LBS

0.02 LBS

3

8

8

GWL-03

GN-03

7

8

3/8" GALV LOCK WASHER

3/8" GALV HEX NUT

C 2023 CommScope, Inc. Confidential


 Δ

	REVISIONS							
REV.	REV. DESCRIPTION		BY	DATE				
A		INITIAL RELEASE	ACG 14JAN06	TP				
В		REPLACE J-BOLT FROM JB-HK	ACG 11DEC08	TP				
С	UPDATE BOM		MSM 15MAY13	TP				
D	U	PDATED TEMPLATES & ADDED SHEE1	LS1146 15MAY23	BCROSS 40171416CMO				
E	-	CHANGED DIMENSION TO BE OUTER FACE OF O OUTER FACE OF RIGHT LEG 20.26" WAS 20.8"	LS1146 10OCT23	EDGAR.BESHAY 40180518CMO				


2

С

D



(2)



.....

40.0[1016.0]

20.0[508.0]

 \square

4

D

С

 $\neg \triangleright$

В

А

3

1.8[44.5]-

20.0[508.0]-

0[0.0]-

