
# 760256239 | C-012-LN-5K-M12BK/15D/B2



Fiber Indoor/outdoor Cable, Low Smoke Zero Halogen / 12 fiber Microsheath, Gel-free , Meters jacket marking, Black jacket color, B2ca flame rating

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

**Product Series** C-LN

General Specifications

Cable Type Stranded microsheath tube

**Subunit Type** Gel-free

Filler, quantity 4

Jacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760256239 12 x 5K 50/125 EN50575

CLASS B ULSZH [Serial number] [metre mark]

Subunit, quantity

Fibers per Subunit, quantity 12

Total Fiber Count 12

Dimensions

 Cable Length
 2000 m | 6,561.68 ft


 Buffer Tube/Subunit Diameter
 1.5 mm | 0.059 in

 Diameter Over Jacket
 6.7 mm | 0.264 in

Representative Image



# 760256239 | C-012-LN-5K-M12BK/15D/B2



## Mechanical Specifications

Minimum Bend Radius, loaded150 mm5.906 inMinimum Bend Radius, unloaded100 mm3.937 inTensile Load, long term, maximum150 N | 33.721 lbf

Tensile Load, short term, maximum 480 N | 107.908 lbf

Cable Crush Resistance, maximum 10 N/mm | 57.101 lb/in

**Compression Test Method** IEC 60794-1-21 E3

**Impact** 2 N-m | 17.701 in lb

Impact Test MethodIEC 60794-1-21 E4Strain Test MethodIEC 60794-1-21 E1

**Twist** 5 cycles

Twist Test Method IEC 60794-1 E7

Optical Specifications

**Fiber Type** OM4, LazrSPEED®

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

**Environmental Specifications** 

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

EN50575 CPR Cable EuroClass Fire Performance B2ca

Page 2 of 3



# 760256239 | C-012-LN-5K-M12BK/15D/B2

EN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd0EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Universal Low Smoke Zero Halogen (ULSZH)

Water Penetration Test Method IEC 60794-1 F5

**Environmental Test Specifications** 

**Temperature Cycle**  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** IEC 60794-1-22 F1

Packaging and Weights

**Cable weight** 49 kg/km | 32.926 lb/kft

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

