

# CSC3-M4D6A1BC000



NOVUX™ CSC100 Compact Fiber Closure, splice/patch, 6 LC/APC duplex adapters, 12 LC/APC pigtails, no splt, Mobra, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®                                  |
| <b>Product Type</b>          | Single-ended, rectangular fiber closure     |
| <b>Product Brand</b>         | NOVUX™                                      |
| <b>Product Series</b>        | CSC 100                                     |

## General Specifications

|                                    |   |
|------------------------------------|---|
| <b>Cable Ports Quantity, total</b> | 3 round ports + 6 multi-out ports (12 cables) |
| <b>Cable Sealing Type</b>          | Compressed gel                                |
| <b>Closure Sealing Type</b>        | Hinged with latch                             |
| <b>Closure Style</b>               | Single-ended                                  |
| <b>Color</b>                       | Black   |
| <b>Mounting</b>                    | Pole   Wall                                   |
| <b>Port Type</b>                   | LC/APC  |
| <b>Port, quantity</b>              | 6   |
| <b>Splitter Type</b>               | No splitter                                   |
| <b>Splitter, quantity</b>          | 0   |

## Dimensions

|               |                    |
|---------------|--------------------|
| <b>Height</b> | 284 mm   11.181 in |
|---------------|--------------------|


# CSC3-M4D6A1BC000

---

**Width** 117 mm | 4.606 in  
**Depth** 77 mm | 3.031 in

# CSC3-M4D6A1BC000

## Dimension Drawing




## Port Configuration

| Position     | Cable diameter            |                                  |
|--------------|---------------------------|----------------------------------|
|              | mm                        | Inches                           |
| Feeder cable | ≤ 14                      | ≤ 0.55                           |
| Branch cable | ≤ 12                      | ≤ 0.47                           |
| Single drops | ≤ 8 (flat cable: 8 x 4,5) | ≤ 0.32 (flat cable: 0.32 x 0.18) |
| Dual drops   | ≤ 6,2                     | ≤ 0.25                           |

## Ordering Tree

# CSC3-M4D6A1BC000



## Environmental Specifications

|                            |               |
|----------------------------|---------------|
| <b>Environmental Space</b> | Outdoor       |
| <b>UV Resistance</b>       | UV stabilized |

## Packaging and Weights

|                           |                   |
|---------------------------|-------------------|
| <b>Included</b>           | Mounting hardware |
| <b>Packaging quantity</b> | 1                 |
| <b>Packaging Type</b>     | Box   Carton      |

## Regulatory Compliance/Certifications

| Agency            | Classification   |
|-------------------|--|
| CHINA-ROHS        | Below maximum concentration value  |
| ISO 9001:2015     | Designed, manufactured and/or distributed under this quality management system |
| ROHS              | Compliant  |
| TL 9000:2016 (R6) | Compliant to this quality management practice                                  |
| UK-ROHS           | Compliant  |



CSC3-M4D6A1BC000

---