## 760256050 | P-096-MZ-5G-F08LM/20T



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Multimode OM5, 96 fiber multiunit with 8 fiber subunits, Lime-green jacket color, Feet cable marking

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MZ

## General Specifications

Armor Type Interlocking aluminum

Cable Type MPO trunk cable

Construction TypeArmoredSubunit TypeGel-freeJacket ColorLime green

Jacket MarkingFeetSubunit, quantity12Fibers per Subunit, quantity8Total Fiber Count96


#### Dimensions

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Armor18.4 mm | 0.724 inDiameter Over Jacket20.5 mm | 0.807 in

## Representative Image



# 760256050 | P-096-MZ-5G-F08LM/20T



### Mechanical Specifications

Minimum Bend Radius, loaded307 mm12.087 inMinimum Bend Radius, unloaded205 mm8.071 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 57 m | 187.008 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

**Environmental Specifications** 

**Installation temperature**  $0 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

Page 2 of 3



# 760256050 | P-096-MZ-5G-F08LM/20T

**Operating Temperature** 0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFCP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 353 kg/km | 237.205 lb/kft

#### Included Products

CS-5G-MP – LazrSPEED® OM5 WideBand Multimode

Fiber

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

