SFG22HDX14-4-H10



G22HDX High Capacity Sector Frame with 2 7/8in OD x 14.5ft face. Includes four 2 7/8in OD x 120in antenna pipes.

Product Classification

Product Type High capacity Tower sector frame

Product Series G2

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Patent Number Patent pending

Pipe, quantity 4
Sectors, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

 Height
 3,048 mm | 120 in

 Face Width
 4.42 m | 14.5 ft

Width 4,419.6 mm | 174 in

Pipe Length 3,048 mm | 120 in

Face Support Pipe Diameter73.025 mm2.875 inMounting Diameter, maximum218.44 mm8.6 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G

ANDREW® an Amphenol company

SFG22HDX14-4-H10

Packaging and Weights

Included Frame | Pipe mounts | Plain end pipes (4) | Stiff arms (2) | Tower attachment

Packaging quantity 1

Weight, net 311.164 kg | 686 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

