

# SFG23HDX-10-B

---



G23HDX High Capacity Sector Frame, 10.5 ft x 2.88 in OD face pipes, Base Kit Only. No antenna pipes.

## Product Classification

<b>Product Type</b>	High capacity Tower sector frame
<b>Product Series</b>	G2

## General Specifications

<b>Mounting</b>	Angle 60°, 203.2 mm (8 in)   Straight or tapered legs up to 203.2 mm (8 in) OD
<b>Patent Number</b>	Patent pending
<b>Pipe, quantity</b>	0
<b>Sectors, quantity</b>	1
<b>Tower Taper</b>	Non-tapered   Tapered

## Dimensions

<b>Face Width</b>	3.2 m   10.5 ft
<b>Width</b>	3,200.4 mm   126 in
<b>Face Support Pipe Diameter</b>	73.025 mm   2.875 in
<b>Mounting Diameter, maximum</b>	218.44 mm   8.6 in
<b>Mounting Diameter, minimum</b>	38.1 mm   1.5 in
<b>Stand-off Distance</b>	1,066.8 mm   42 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact your local ANDREW representative
<b>Wind Rating Test Method</b>	TIA/EIA-222-G

## Packaging and Weights

<b>Included</b>	Frame   Stiff arms (2)   Tower attachment
-----------------	---

# SFG23HDX-10-B

---

**Packaging quantity** 1

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code