

Fiber indoor/outdoor cable, OFNR/LSZH Riser Rollable Ribbon Dual Rated Backbone, 144 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Cca flame rating

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series N-MP

General Specifications

 Cable Type
 Riser rated low smoke

Construction Type Non-armored

Subunit Type Gel-free

Fibers per Ribbon, quantity 12

Jacket Color Black

Jacket Marking Feet


Total Fiber Count 144

Dimensions

Diameter Over Jacket 9.2 mm | 0.362 in

Representative Image





Mechanical Specifications

Minimum Bend Radius, loaded 184 mm | 7.244 in

Minimum Bend Radius, unloaded74 mm2.913 inTensile Load, long term, maximum396 N89.024 lbf

Tensile Load, short term, maximum 1320 N | 296.748 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Page 2 of 4

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-104-696 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR (UL) and c(UL)

Flame Test Method FT4 | UL 1666

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend -10 °C to +60 °C (+14 °F to +140 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 90.6 kg/km | 60.88 lb/kft

Regulatory Compliance/Certifications

Agency Classification ANATEL Compliant

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8G1-RR-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Rollable

Ribbon Fiber (ITU-T G.657.A2, B2)



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable