



Propel Singlemode Splice Cassette, 12LC/UPC with internal shutters, OS2 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 4 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	16

Dimensions

Height	67.31 mm 2.65 in
Width	131.013 mm 5.158 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

760255051 | PPL-SP-16LC-SM-RPT-BEU

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard UL

Packaging and Weights

Included Single Fusion Splice Protection Sleeves

Packaging quantity 1

Included Products

FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack