



Propel Singlemode Splice Cassette, 12LC/APC with internal shutters, OS2 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

|                       |   |
|-----------------------|---|
| Regional Availability | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| Portfolio             | CommScope®  |
| Product Type          | Fiber cassette with ribbon pigtail                                  |
| Product Brand         | Propel  |
| Product Series        | PPL   |

General Specifications

|                        |                         |
|------------------------|-------------------------|
| Color, front           | Green                   |
| Interface, front       | LC/APC                  |
| Interface, rear        | Ribbon pigtail          |
| Polarity               | Method B Enhanced (ULL) |
| Shuttered              | Yes                     |
| Total Fibers, quantity | 12                      |

Dimensions

|        |                      |
|--------|----------------------|
| Height | 67.31 mm   2.65 in   |
| Width  | 97.993 mm   3.858 in |

Optical Specifications

|                         |            |
|-------------------------|------------|
| Fiber Mode              | Singlemode |
| Fiber Type              | G.657.A2   |
| Insertion Loss, maximum | 0.25 dB    |

Environmental Specifications

|                         |                           |
|-------------------------|---------------------------|
| Qualification Standards | IEC 61753-1   TIA-568.3-D |
| Safety Standard         | UL                        |

Packaging and Weights

|                    |   |
|--------------------|---|
| Included           | Single Fusion Splice Protection Sleeves |
| Packaging quantity | 1                                       |

Regulatory Compliance/Certifications

| Agency     | Classification                    |
|------------|-----------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| ROHS       | Compliant                         |
| UK-ROHS    | Compliant                         |

