	4	3		\bigvee
D	 1.0 GENERAL NOTES 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X] 1.2 FOR PATENT INFO: https://www.cs-pat.com 2.0 DESIGN NOTES 2.1 ANY HAZARDS OR OBSTRUCTIONS TO THE CLIMBING FACILITY AND IDENTIFIED PRIOR TO INSTALLING THE APPURTENANCE. ADDITIONAR REQUIRED TO MAINTAIN THE INTEGRITY OF THE SAFETY CLIMB. DU TEMPORARY AND/OR PERMANENT PRECAUTIONARY MEASURES SH PRESERVE THE CLIMBING FACILITY AND/OR SAFETY CLIMB. 3.0 MANUFACTURING/SPECIAL REQUIREMENTS 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DEACH LEG OF THE U-BOLT. 4.0 TEST 5.0 PACKAGING 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCU 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED 	AL PRODUCTS MAY BE JRING INSTALLATION, HOULD BE TAKEN TO I METHOD. TIGHTEN ALL U-BOLTS DISTANCE AND EQUAL FORCE ON MENT IS-PL-3005		
		00		
С	STRAP FOR REFERE	ENCE		
В			PB0308G	

А

3


_	
\frown	
/	
_	


	REVISIONS			
REV.		DESCRIPTION	DATE	APPROVED
A		NEW RELEASED.	XZ1054 08MAR21	10276PC
В	DIA	GONAL BRACES CONNECTING FRNT FACE TO BASE THICKENED	DRF 02APR21	11454PC
С		CLEANED UP SAP BOMs AND DRAWING	RJC 24JUN21	13393PC
D	ļ	ADDED TABLE 2 & NEW MID RF-NL10-BDSH	AZ1030 11AUG21	40138457CMO
E	UPD	ATED PACKAGE VIEW AND STRUCTURE VIEW	JL1183 280CT24	CJMANN 40207662CMO


D


С

В









ITEM	PART NO.	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
1	RF-NL10-BDSH	SECTOR FRAME, ROOF TOP, 10 FT FACE, HD	1	603.88 LBS	
2	MT54796	3.5" O.D. X 96" PIPE	3	48.54 LBS	