## UHGMXMXCK

**Base Product** 



#### Singlemode MPO12 APC (pinned) to MPO12 APC (pinned) Fiber Trunk Cable Assembly, 72-Fiber, Armored Indoor Plenum

### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America	
Portfolio	CommScope®	
Product Type	Fiber trunk cable assembly	
Product Brand	Propel   SYSTIMAX ULL	
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration	

### General Specifications

Connector A, quantity	6
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	6
Color, boot B	Black
Color, connector B	Green
Construction Type	Armored   Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Male
Interface, Connector B	MPO-12/APC Male
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	72
Dimensions	
Cable Assembly Length Range (m)	3 – 305

Page 1 of 8



## UHGMXMXCK

Cable Assembly Length Range (ft)

10 - 999

### Ordering Tree

BASE	CODE			·
acket Color				<u> </u>
		Breakout Length / Option		ength
Yellow	В	metal gland		
	С	with pulling grip		
	z	36 inch extension with shelf mount, gland		
	Y	36 inch extension with shelf mount, gland, pulling grip		моц
	J	23 inch breakout, with mounting clips	F	Feet
	к	23 inch breakout, with mounting clips, pulling grip both ends	М	Meter
	R	23 inch breakout, with 36 inch extension, mounting clips		
	s	23 inch breakout, with 36 inch extension mounting clips, pulling grip both ends		
	L	23 inch breakout, with 72 inch extension mounting clips		
	м	23 inch breakout, with 72 inch extension, mounting clips, pulling grip both ends		

### Mechanical Specifications

 Cable Retention Strength, maximum
 11.24 lb @ 0 ° | 4.40 lb @ 90 °

### Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

#### **Environmental Specifications**

Operating Temperature Environmental Space -10 °C to +60 °C (+14 °F to +140 °F)

Indoor | Plenum

Page 2 of 8



# UHGMXMXCK

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



760242071 P-072-MZ-8G-F12YL/20T	-	Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 72 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
860659010	-	MPO-12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm



# 760242071 | P-072-MZ-8G-F12YL/20T



Fiber indoor cable, Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 72 fiber multi-unit with 12 fiber subunits, Gel-free, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

### Product Classification


Regional Availability	Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	P-MZ
General Specifications	
Armor Type	Interlocking aluminum
Cable Type	MPO trunk cable
Construction Type	Armored
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Feet
Subunit, quantity	6
Fibers per Subunit, quantity	12
Total Fiber Count	72
Dimensions	
Buffer Tube/Subunit Diameter	2 mm   0.079 in
Diameter Over Armor	15.9 mm   0.626 in
Diameter Over Jacket	17.9 mm   0.705 in

### Representative Image

Page 4 of 8



## 760242071 | P-072-MZ-8G-F12YL/20T



#### Mechanical Specifications

Minimum Bend Radius, loaded	269 mm   10.591 in
Minimum Bend Radius, unloaded	179 mm   7.047 in
Tensile Load, long term, maximum	200 N   44.962 lbf
Tensile Load, short term, maximum	667 N   149.948 lbf
Compression	85 N/mm   485.363 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	35 N-m   309.776 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	75 m   246.063 ft
Optical Specifications	
Fiber Type	G.657.A2/B2   G.657.A2/B2

#### **Environmental Specifications**

Installation temperature

0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 8



# 760242071 | P-072-MZ-8G-F12YL/20T

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-409
Environmental Space	Plenum
Flame Test Listing	NEC OFCP (ETL) and c(ETL)
Flame Test Method	NFPA 130   NFPA 262

#### **Environmental Test Specifications**

Heat Age	0 °C to +85 °C (+32 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	0 °C to +70 °C (+32 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	0 °C to +70 °C (+32 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

### Packaging and Weights

Cable weight

272 kg/km | 182.776 lb/kft

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 6 of 8



## 860659010



### MPO-12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	TeraSPEED®
General Specifications	
Color	Green
Color, boot	Black
Ferrule Geometry	Angled
Interface	MPO/APC Male
Interface Feature	Pinned
Total Fiber Count	12
Dimensions	
Compatible Cable Diameter	2 mm   0.079 in
Material Specifications	
Ferrule Material	Polymer
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.657.A2
Optical Components Standard	ANSI/TIA-568-C.3
Insertion Loss, ULL, maximum	0.35 dB
Return Loss, minimum	65 dB

### Packaging and Weights

Page 7 of 8



860659010

**Packaging quantity** 

1

Page 8 of 8

