UHVMXUCCF

Base Product



Ultra Low Loss (ULL) OM5 MPO12 UPC (pinned) to Unconnectorized Fiber Trunk Cable Assembly, 24-Fiber, Armored Indoor Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Connector A, quantity 2

Color, boot A Black

Color, connector A Lime green

Connector B, quantity 0

Construction Type Armored | Stranded

Furcation Color Lime green

Interface, Connector A MPO-12/UPC Male

Interface, Connector BUnterminatedJacket ColorLime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions

Breakout Length 22 in


Cable Assembly Length Range (m) 3 – 305

Cable Assembly Length Range (ft) 10 – 999

COMMSCOPE®

UHVMXUCCF

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Indoor | Plenum

Regulatory Compliance/Certifications

COMMSCOPE®

UHVMXUCCF

Agency Classification

ANATEL Compliant

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

760242129 – Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with P-024-MZ-5G-F12LM/20T plenum jacket, 24 fiber with 12 fiber subunits, Gel-free, Multimode OM5, Feet jacket marking,

Lime green jacket color

860659008 – MPO12, ULL, MALE, OM5, LIME, 2MM



760242129 | P-024-MZ-5G-F12LM/20T



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, 24 fiber with 12 fiber subunits, Gel-free, Multimode OM5, Feet jacket marking, Lime green jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MZ

General Specifications

Armor Type Interlocking aluminum

Cable Type MPO trunk cable

Construction TypeArmoredSubunit TypeGel-free

Filler, quantity 2

Jacket Color Lime green

Jacket MarkingFeetSubunit, quantity2Fibers per Subunit, quantity12Total Fiber Count24

Dimensions


Buffer Tube/Subunit Diameter 2 mm | 0.079 in

Diameter Over Armor14.61 mm | 0.575 inDiameter Over Jacket16.6 mm | 0.654 in

Representative Image



760242129 | P-024-MZ-5G-F12LM/20T



Mechanical Specifications

Minimum Bend Radius, loaded250 mm9.843 inMinimum Bend Radius, unloaded166 mm6.535 inTensile Load, long term, maximum200 N | 44.962 lbfTensile Load, short term, maximum667 N | 149.948 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 89 m | 291.995 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 8



760242129 | P-024-MZ-5G-F12LM/20T

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFCP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle 0 °C to +70 °C (+32 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 229 kg/km | 153.881 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860659008



MPO12, ULL, MALE, OM5, LIME, 2MM

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface FeaturePinnedTotal Fiber Count12

Dimensions

Length 60.1 mm | 2.366 in Compatible Cable Diameter 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 $^{\circ}$

Optical Specifications

Fiber Mode Singlemode

Fiber Type OM5, LazrSPEED®

Insertion Loss Change, mating 0.2 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

860659008

 Insertion Loss, maximum
 0.2 dB

 Return Loss, minimum
 27 dB

Packaging and Weights

Packaging quantity 1

* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

