


MTC3752T3HD



G22HD Series High Capacity Three Sector Frame Kit for Towers, 12.5 ft x 2.88 in OD face pipes, includes twelve 96 in x 2.38 OD antenna pipes plus six 96 in RRU Pipes

Product Classification

Product Type	High capacity Tower sector frame
Ordering Note	NSTD445 Compliant

General Specifications

Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	18
Tower Taper	Non-tapered Tapered

Dimensions

Height	2,438.4 mm 96 in
Face Width	3.81 m 12.5 ft
Width	3,810 mm 150 in
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	50.8 mm 2 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	1,092.2 mm 43 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222-G

MTC3752T3HD

Packaging and Weights

Included	Frame Pipe mounts Plain end pipes (12) RRU Pipes (6) Stiff arm Tower attachment
Packaging quantity	1
Weight, net	886.319 kg 1954 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--