

NOVUX™ Hardened Tap Terminal, 60/40, 11 dB, One Input port, 4 drop ports and one Through port, Stubless

- NOVUX™ Hardened Tap Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ HTT terminals are available in 2-port, 4-port and 8-port models, depending on the number of drop ports required. Each model is available with a range of tap values depending on how much optical power should be dropped off at each location
- Available with flat dielectric and flat toneable/locatable dielectric cable
- NOVUX™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Product Type Access terminal, with splitter/tap

Product Brand NOVUX™

Product Series HTT

Minimum Order Quantity 1

General Specifications

Distribution Type 4-port tap

Drop Port TypeHardened full-size SC/APC

Enclosure Color Black (RAL 9005)

Input Tap, quantity

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened full-size SC/APC

Split Ratio 60/40
Stub Type No tail
Tap Ports, quantity 4

Thru Tap, quantity



Dimensions


 Height
 80.5 mm | 3.169 in


 Width
 157.92 mm | 6.217 in

 Length
 193.17 mm | 7.605 in

Cable Length, stub 0 ft (0 m)

Dimension Drawing






Port Configuration

NOVUXHT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
HTT Series	Optical taps	2 drops	4 drops	8 drops

Ordering Tree





Material Specifications

Enclosure Material Type Hardened plastic

Optical Specifications

Tap Value

Operating Wavelength Range 1260 – 1635 nm

Attenuation Single Ports, maximum6 dBTap Drop Loss, maximum12.7 dBTap Thru Loss, maximum3.5 dB

Environmental Specifications

Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)

Relative Humidity 5%-100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G | Telcordia GR-771-CORE,

Issue 2

11 dB

UV Resistance UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Page 3 of 4

Regulatory Compliance/Certifications

Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

