

# HTT-B2AG000000U000



NOVUX™ Prodigy™ Hardened Tap Terminal, 80/20, 12 dB, One Input port, 2 drop ports and one Through port, Stubless, with universal mounting bracket

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug-and-play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ Prodigy™ HTT Tap terminals are available in 2-port, 4-port and 8-port models, depending on the number of drop ports required. Each model is available with a range of tap values depending on how much optical power should be dropped off at each location
- HTT tap terminals are stubless with a Prodigy™ Input port and a Through Port for non-terminating taps
- NOVUX™ Prodigy™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ Prodigy™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

## Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Product Type	Access terminal, with tap
Product Brand	NOVUX™
Product Series	HTT
Minimum Order Quantity	1


## General Specifications

Cable Type	No cable (stubless)
Distribution Type	2-port tap
Drop Port Type	Hardened Prodigy SC/APC
Enclosure Color	Black (RAL 9005)
Forward Port Type	Hardened Prodigy SC/APC
Forward Port, quantity	1
Input Tap, quantity	1
Mounting	Handhole   Pedestal   Pole   Strand
Port Type	Hardened Prodigy SC/APC

# HTT-B2AG0000000U000

Split Ratio	80/20
Stub Type	No tail
Tap Ports, quantity	2
Thru Tap, quantity	1
Dimensions	
Height	80 mm   3.15 in
Width	78.94 mm   3.108 in
Length	161.42 mm   6.355 in

## Dimension Drawing



## Ordering Tree

HTT- [ ] [ ] H [ ] 0 0000 0 [ ] 000

**Housing color**

B Black, RAL 9005

G Gray, RAL 7035

**Number of drop ports**

2 2 port

4 4 port

8 8 port

**Adapter type**

H Full-size

**Tap configurations**

A 21 dB

B 19 dB

C 17 dB

D 15 dB

E 14 dB

F 13 dB

G 12 dB

H 11 dB

J 11 dB terminating

K 10 dB

L 9 dB

M 8 dB

N 7 dB

P 7 dB terminating

Q 5 dB

R 4 dB terminating

S 22 dB

**Customization**

000 Standard

**Accessories**

N No accessories

U Universal bracket

S Strand bracket

P Universal cable bracket

**Stub end**

0 Stubless

**Cable length**

0000 0 ft, 0 m

**Cable type**

0 Stubless

<b>Enclosure Material Type</b>	Hardened plastic
--------------------------------	------------------

# HTT-B2AG000000U000

Operating Wavelength Range	1260 – 1635 nm
Attenuation Terminal Connectors, maximum	0.4 dB
Tap Drop Loss, maximum	12.4 dB
Tap Thru Loss, maximum	2.1 dB
Tap Value	12 dB

## Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground   Below ground
Qualification Standards	IEC 60529, IP68 + 2 m waterhead   IEC 61753-1, category G   Telcordia GR-771-CORE, Issue 2
UV Resistance	UV stabilized

## Packaging and Weights

Included	Universal mounting bracket
Packaging quantity	1
Packaging Type	Box

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

