## SF-DPM-B



#### Co-location Dual Pipe Mount Base Kit, pipe ordered separately

#### **Product Classification**

**Product Type**Co-location dual pipe mount kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

**Note** Two 72 in x 8 in panel antenna per sector

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

**Dimensions** 

 Height
 254 mm | 10 in

 Face Width
 1.463 m | 4.8 ft

**Width** 1,447.8 mm | 57 in

**Length** 0.396 m | 1.3 ft

Face Support Pipe Diameter 88.9 mm | 3.5 in

Mounting Diameter, maximum 203.2 mm | 8 in

**Mounting Diameter, minimum** 0 mm | 0 in

**Stand-off Distance** 391.16 mm | 15.4 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Test Method TIA/EIA-222

### Packaging and Weights



# SF-DPM-B

Included Frame | Saddle mount

Packaging quantity 1

**Weight, net** 59.7 kg | 131.616 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

