SF-DPM2-84



Co-location Dual Pipe Mount Kit; includes (2) 2-3/8 in OD x 84 in pipes

Product Classification	
Product Type	Co-location dual pipe mount kit
General Specifications	
Mounting	Angle 60°, 203.2 mm (8 in) Angle 90°, 152.4 mm (6 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Note	Two 72 in x 8 in panel antenna per sector
Pipe, quantity	2
Tower Taper	Non-tapered Tapered
Dimensions	
Height	2,133.6 mm 84 in
Face Width	1.463 m 4.8 ft
Width	1,447.8 mm 57 in
Length	0.396 m 1.3 ft
Pipe Length	2,133.6 mm 84 in
Face Support Pipe Diameter	88.9 mm 3.5 in
Mounting Diameter, maximum	203.2 mm 8 in
Mounting Diameter, minimum	0 mm 0 in
Pipe Outer Diameter	60.96 mm 2.4 in
Stand-off Distance	391.16 mm 15.4 in
Material Specifications	
Material Type	Hot dip galvanized steel
Mechanical Specifications	
Wind Rating	120 mph (BWS) at 150 ft AGL 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Test Method

TIA/EIA-222

Page 1 of 2



SF-DPM2-84

Packaging and Weights

Included	Clamps Frame Pipe mounts Pipes Saddle mounts
Packaging quantity	1
Weight, net	118.9 kg 262.129 lb
Regulatory Compliance/Certifications	
Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
* Footnotes	

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

ANDREW

an Amphenol company

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025