

NOVUX[™] Prodigy[™] Hardened Indexing Terminal, Prodigy Adapter ports, 12F, 1:4 Splitter, 1 HMFOC port, Three 1F multi-use, 1 Reverse HMFOC port, Dielectric flat loose tube, 100 ft/30 m HMFOC Plug (female/no pin) tail, with mounting bracket

- NOVUX[™] Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug-and-play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX[™] Prodigy[™] HXT fiber indexing terminals are available with 1:4 or 1:8 splitter and optional multi-use ports, Index Only and Index Branching 2 to 6 fiber solutions
- Available stubless or with flat dielectric and flat toneable/locatable dielectric cable with HMFOC Plug (female/no pin)
- NOVUX[™] Prodigy[™] smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ Prodigy™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Access terminal, with splitter/tap
Product Brand	NOVUX™
Product Series	HXT
Minimum Order Quantity	1
General Specifications	
Cable Type	Dielectric - Flat - Loose Tube
Cable, quantity	1
Distribution Type	1 x 4 splitter + multi-use ports (3)
Drop Port Type	Hardened Prodigy SC/APC
Drop Port, quantity	6
Enclosure Color	Black (RAL 9005)
Forward Port Type	Hardened multi-fiber (HMFOC) jack, male/pinned
Forward Port, quantity	1
Mounting	Handhole Pedestal Pole Strand



Port, quantity9Reverse Port TypeHardened multi-fiber (HMFOC) jack, male/pinnedReverse Port, quantity1Splitter, quantity1Splitter, quantityHardened multi-fiber (HMFOC) plug, female/no pinStub TypeHardened multi-fiber (HMFOC) plug, female/no pinDimensions1Height80 mm 3.14 inWidth128 mm 5.03 inLength207 mm 8.14 inCable Length, stub100 ft (30 m)Gable Outer Diameter4.3 x 80 mm (0.17 x 0.31 in) in	Port Type	Hardened Prodigy SC/APC
Reverse Port, quantity1Splitter, quantity1Stub TypeHardened multi-fiber (HMFOC) plug, female/no pinDimensions80 mm 3.14 inWidth128 mm 5.03 inLength207 mm 8.14 inCable Length, stub100 ft (30 m)	Port, quantity	9
Splitter, quantity1Stub TypeHardened multi-fiber (HMFOC) plug, female/no pinDimensions80 mm 3.14 inWidth128 mm 5.03 inLength207 mm 8.14 inCable Length, stub100 ft (30 m)	Reverse Port Type	Hardened multi-fiber (HMFOC) jack, male/pinned
Stub TypeHardened multi-fiber (HMFOC) plug, female/no pinDimensions80 mm 3.14 inWidth128 mm 5.03 inLength207 mm 8.14 inCable Length, stub100 ft (30 m)	Reverse Port, quantity	1
Dimensions Height 80 mm 3.14 in Width 128 mm 5.03 in Length 207 mm 8.14 in Cable Length, stub 100 ft (30 m)	Splitter, quantity	1
Height 80 mm 3.14 in Width 128 mm 5.03 in Length 207 mm 8.14 in Cable Length, stub 100 ft (30 m)	Stub Type	Hardened multi-fiber (HMFOC) plug, female/no pin
Width 128 mm 5.03 in Length 207 mm 8.14 in Cable Length, stub 100 ft (30 m)	Dimensions	
Length 207 mm 8.14 in Cable Length, stub 100 ft (30 m)	Height	80 mm 3.14 in
Cable Length, stub100 ft (30 m)	Width	128 mm 5.03 in
	Length	207 mm 8.14 in
Cable Outer Diameter 4.3 x 8.0 mm (0.17 x 0.31 in) in	Cable Length, stub	100 ft (30 m)
	Cable Outer Diameter	4.3 x 8.0 mm (0.17 x 0.31 in) in

Dimension Drawing





Page 2 of 4



Port Configuration

NOVUX HT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
	12 fiber index only, 1f	12 fiber 1:4	12 fiber 1:8	
	HXT Series Fiber indexing	12 fiber index only, 2f	12f multi-use 2f + 1:4	12 fiber multi-use, 3f +1:4
		12 fiber index only, 3f	24f multi-use 2f	12 fiber multi-use, 4f +1:4
HXT Series		12 fiber index only, 4f	24f multi-use 3f	12 fiber multi-use, 2f +1:8
	12 fiber multi-use, 2f	24f multi-use 4f		
	12 fiber branching, 2 to 6f per port			

Ordering Tree



Material Specifications

Enclosure Material Type

Hardened plastic

Optical Specifications

Fiber Type	G.657.A1/A2
Operating Wavelength Range	1260 – 1635 nm
Attenuation Single Ports, maximum	7.5 dB
Attenuation Cable Coefficient, maximum	0.30 dB/km @ 1550 nm 0.40 dB/km @ 1310 nm

Page 3 of 4



Insertion Loss, Splitter, maximum	7.1 dB
Insertion Loss, Stub Connector, maximum	0.65 dB
Return Loss, Connector, maximum	65 dB
Return Loss, Single Ports, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground Below ground
Qualification Standards	IEC 60529, IP68 + 2 m waterhead IEC 61753-1, category G
UV Resistance	UV stabilized
Packaging and Weights	
Included	Universal mounting bracket
Packaging quantity	1
Packaging Type	Box Coiled

Regulatory Compliance/Certifications

Æ

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



