MC-CP14M-12-96-J



3-Sector Adjustable Monopole Co-location Platform Kit, 15 in to 50 in OD, 14 ft 6 in face, includes twelve 96 in pipes

Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

Dimensions

 Height
 2,438.4 mm | 96 in

 Face Width
 4.42 m | 14.5 ft

 Width
 4,419.6 mm | 174 in

 Pipe Length
 2,438.4 mm | 96 in

 Face Support Pipe Diameter
 73.152 mm | 2.88 in

 Mounting Diameter, maximum
 1270 mm | 50 in

 Mounting Diameter, minimum
 381 mm | 15 in

Material Specifications

Pipe Outer Diameter

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Plain end pipes (12) | Platform | Rail | Ring mount

60.452 mm | 2.38 in

Packaging quantity 1

COMMSCOPE®

MC-CP14M-12-96-J

Weight, net

809.209 kg | 1784 lb

