Base Product



0.6 m | 2 ft ValuLine® High Performance Low Profile Antenna, dual band, dual polarised 71.000 - 86.000 GHz and dual polarised, 21.200 -23.600 GHz

Product Classification

Product Type Microwave antenna

Product Brand ValuLine®

General Specifications

Antenna Type VHLP - ValuLine® High Performance Low Profile Antenna, dual band

Polarization Dual 80 GHz, Dual 23 GHz

Side Struts, Included 0 Side Struts, Optional 0

Dimensions

Diameter, nominal 0.6 m | 2 ft

Electrical Specifications

71.000 - 86.000 GHz **Operating Frequency Band**

48.5 dBi Gain, Low Band Gain, Mid Band 49.5 dBi Gain, Top Band 50 dBi **Boresite Cross Polarization Discrimination (XPD)** 30 dB Front-to-Back Ratio 68 dB Beamwidth, Horizontal 0.5° Beamwidth, Vertical 0.5° **Return Loss** 15 dB **VSWR** 1.43 Radiation Pattern Envelope Reference (RPE)

Electrical Compliance ETSI 302 217 Class 3 | US FCC Part 101.115

7442B



Electrical Specifications, Band 2

Operating Frequency Band 21.200 – 23.600 GHz

Gain, Low Band39.3 dBiGain, Mid Band39.4 dBiGain, Top Band39.5 dBiBeamwidth, Horizontal1.5 °Beamwidth, Vertical1.5 °Boresite Cross Polarization Discrimination (XPD)30 dB

Electrical Compliance Canada SRSP 321.8 B | ETSI 302 217 Class 3 | FCC Cat A

Front-to-Back Ratio 66 dB
Radiation Pattern Envelope Reference (RPE) 7441
Return Loss 15 dB
VSWR 1.43

Mechanical Specifications

Compatible Mounting Pipe Diameter 50 mm – 120 mm | 2.0 in – 4.7 in

Fine Azimuth Adjustment Range $\pm 8^{\circ}$ Fine Elevation Adjustment Range $\pm 15^{\circ}$


 Wind Speed at 23 GHz, operational
 180 km/h | 111.847 mph

 Wind Speed at 80 GHz, operational
 144 km/h | 89.477 mph

 Wind Speed, survival
 250 km/h | 155.343 mph

Antenna Dimensions and Mounting Information





Dimensions in mm (Inches)						
Antenna Size, ft (m)	Α	В	С	D	E	F
2 (0.6)	660 (25.9)	309 (12.2)	283 (11.1)	106 (4.2)	462 (18.2)	505 (19.8)

Wind Forces at Wind Velocity Survival Rating


Axial Force (FA) 1693 N | 380.602 lbf

Side Force (FS) 814 N | 182.995 lbf

Twisting Moment (MT) 756 N-m | 6,691.164 in lb

Zcg without Ice 9 mm | 0.354 in

Wind Forces at Wind Velocity Survival Rating Image



Packaging and Weights

Weight, net 17 kg | 37.479 lb

* Footnotes

Operating Frequency Band

Bands correspond with CCIR recommendations or common allocations

used throughout the world. Other ranges can be accommodated on

special order.

Gain, Mid BandFor a given frequency band, gain is primarily a function of antenna size.

The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Boresite Cross Polarization Discrimination (XPD) The difference between the peak of the co-polarized main beam and the

maximum cross-polarized signal over an angle twice the 3 dB beamwidth

ANDREW® an Amphenol company

of the co-polarized main beam.

Front-to-Back Ratio Denotes highest radiation relative to the main beam, at 180° ±40°, across

the band. Production antennas do not exceed rated values by more than 2

dB unless stated otherwise.

Return LossThe figure that indicates the proportion of radio waves incident upon the

antenna that are rejected as a ratio of those that are accepted.

VSWR Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the

operating band.

Radiation Pattern Envelope Reference (RPE)

Radiation patterns define an antenna's ability to discriminate against

unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining

an angular accuracy of +/-1° throughout

Radiation Pattern Envelope Reference (RPE)Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not

have any peak exceeding the current RPE by more than 3dB, maintaining

an angular accuracy of +/-1° throughout

Wind Speed, survival

The maximum wind speed the antenna, including mounts and radomes,

where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna

with the specified amount of radial ice.

Axial Force (FA)Maximum forces exerted on a supporting structure as a result of wind

from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are

referenced to the mounting pipe.

Side Force (FS)Maximum side force exerted on the mounting pipe as a result of wind from

the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the

mounting pipe.

Twisting Moment (MT)Maximum forces exerted on a supporting structure as a result of wind

from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are

referenced to the mounting pipe.