


# TFL-M2-14



Tower Face Mount with dual 14 ft x 2-3/8 in OD face pipe supports, includes pipe

## Product Classification

**Product Type** Tower face mount

## General Specifications

**Mounting** Angle 60°, 406.4 mm (16 in) | Angle 90°, 304.8 mm (12 in) | Straight or tapered legs up to 406.4 mm (16 in) OD

**Pipe, quantity** 1

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 1,600.2 mm | 63 in

**Face Width** 4,267 m | 14 ft

**Width** 4,267.2 mm | 168 in

**Length** 304.8 mm | 12 in

**Pipe Length** 1,600.2 mm | 63 in

**Face Support Pipe Diameter** 60.96 mm | 2.4 in

**Mounting Diameter, maximum** 406.4 mm | 16 in

**Mounting Diameter, minimum** 0 mm | 0 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

# TFL-M2-14

---

Included	Crossover plates   Pipes   Saddle mounts
Packaging quantity	1
Weight, net	234.19 kg   516.3 lb

\* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
-------------	--