F1-CLAMP-2B



✓ KwikClamp[™] Hanger for 1/4 in superflexible coaxial cable, double stack; includes hardware

Product Classification

Product Type	Hanger kit	
Product Brand	KwikClamp™	
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box	
General Specifications		
Cables per Hanger	1	
Color	Black	
Hanger Type	KwikClamp™ hanger	
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8- 25 mm	
Dimensions		
Maximum Stack Height	2	
Height	114 mm 4.488 in	
Width	22 mm 0.866 in	
Length	42 mm 1.654 in	
Compatible Diameter, maximum	9 mm 0.354 in	

Compatible Diameter, minimum

- Nominal Size
- Hanger Spacing, maximum

Electrical Specifications

Return Loss Effect, maximum	
DTF Effect, maximum	

Material Specifications

Material Type

Engineered plastic | Stainless steel

7 mm | 0.276 in

1.83 m | 6.004 ft

1/4 in

0.1 dB

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025

F1-CLAMP-2B

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

-40 °C to +70 °C (-40 °F to +158 °F)	
≥500 hours in salt spray chamber	
Five times cable weight	
≥100 hours exposure in accelerated UV life chamber	

Packaging and Weights

Height, packed	15.5 cm 6.102 in
Width, packed	30.5 cm 12.008 in
Length, packed	35.5 cm 13.976 in
Included	Hardware
Packaging quantity	108
Weight, gross	8.6 kg 18.96 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power



Page 2 of 2

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025