L4-CLAMP-3B



── KwikClamp™ Hanger for 1/2 in coaxial cable, triple stack; includes hardware

Product Classification

Product TypeHanger kitProduct BrandKwikClamp™

Ordering Note ANDREW® standard product in Europe, the Middle East, and

Africa | Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger

Color Black

Hanger Type KwikClamp™ hanger

Mounting 3-25 mm angle iron | 3-25 mm flat plate | Round Member 8-

25 mm

Dimensions

Maximum Stack Height 3

 Height
 170 mm | 6.693 in

 Width
 32 mm | 1.26 in

 Length
 42 mm | 1.654 in

 Compatible Diameter, maximum
 17 mm | 0.669 in

 Compatible Diameter, minimum
 15 mm | 0.591 in

Nominal Size 1/2 in

Hanger Spacing, maximum 1.83 m | 6.004 ft

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic | Stainless steel

ANDREW® an Amphenol company

L4-CLAMP-3B

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Corrosion Resistance, minimum with no degredation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15.5 cm | 6.102 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 48

Weight, gross 7.7 kg | 16.976 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

