


F-CLAMP-A2A2CC-4B



KwikClamp™ Hanger for power & fiber cables, one 7-9 mm hole and one 22-34 mm hole (alongside each other), quadruple block; includes hardware

Product Classification

Product Type	Hanger kit
Product Brand	KwikClamp™
Ordering Note	ANDREW® standard product in Europe, the Middle East, and Africa Minimum order quantity (MOQ) is 1 box

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	KwikClamp™ hanger
Mounting	3–25 mm angle iron 3–25 mm flat plate Round Member 8-25 mm

Dimensions

Maximum Stack Height	4
Height	224 mm 8.819 in
Width	44 mm 1.732 in
Length	45 mm 1.772 in
Compatible Cable Diameter Range	22–34 mm 7–9 mm
Diameter Range (cable 1)	7–9 mm
Diameter Range (cable 2)	22–34 mm
Hanger Spacing, maximum	1.83 m 6.004 ft

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	EPDM rubber Engineered plastic Stainless steel
---------------	--

F-CLAMP-A2A2CC-4B

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -45 °C to +70 °C (-49 °F to +158 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Five times cable weight

UV Resistance, minimum with no degradation ≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

Packaging and Weights

Height, packed 15.5 cm | 6.102 in

Width, packed 30.5 cm | 12.008 in

Length, packed 35.5 cm | 13.976 in

Included Hardware

Packaging quantity 24

Weight, gross 6.9 kg | 15.212 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power