

16-port sector antenna, 4x 694-960, 4x 1427-2690 MHz, 65° HPBW and 8x 1695-2690 MHz, 90° HPBW, 5x RET

- Antenna FDD Beamforming in 1695-2690 MHz
- Soft Split Feature available
- Antenna support 4T4R configuration by using external power divider
- V4 array uses MQ4/5 cluster connectors

### General Specifications

Antenna Type Sector and beamforming

**Band** Multiband

Calibration Connector Interface MQ5
Calibration Connector Quantity 1

**Grounding Type**RF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

**RF Connector Interface** 4.3-10 Female | MQ4 | MQ5

**RF Connector Location** Bottom

RF Connector Quantity, high band 0

RF Connector Quantity, mid band 12

RF Connector Quantity, low band 4

RF Connector Quantity, total 16

### Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET Low band (2) | Mid band (3)

Power Consumption, active state, maximum  $8~\mathrm{W}$  Power Consumption, idle state, maximum  $1~\mathrm{W}$ 

**Protocol** 3GPP/AISG 2.0

**Dimensions** 

ANDREW® an Amphenol company

Page 1 of 6


**Width** 498 mm | 19.606 in

**Depth** 197 mm | 7.756 in

**Length** 2688 mm | 105.827 in

Net Weight, antenna only 45.2 kg | 99.649 lb

### Array Layout



Array ID	Frequency (MHz)	RF Connector	HPBW	RET (SRET)	AISG No.	AISG RET UID
R1	694-960	1 - 2	65°	1	AISG1	CPxxxxxxxxxxxxxR1
R2	694-960	3 - 4	65°	2	AISG1	CPxxxxxxxxxxxxxR2
Y1	1427-2690	5 - 6	65°	3	AISG1	CPxxxxxxxxxxxxxY1
Y2	1427-2690	7 - 8	65°	4	AISG1	CPxxxxxxxxxxxxxY2
Y3	1695-2690	9 - 16	BF°	5	AISG1	CPxxxxxxxxxxxxxXY3

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration



### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1427 – 2690 MHz | 1695 – 2690 MHz | 694 – 960 MHz

Polarization ±45°

**Total Input Power, maximum** 900 W @ 50 °C

## **Electrical Specifications**

	R1,R2	R1,R2	R1,R2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	698-806	790-894	890-960	1427-151	8 1695–199	5 1920-230	0 2300-250	0 2490-2690
RF Port	1-4	1-4	1-4	5-8	5-8	5-8	5-8	5-8
Gain at Mid Tilt, dBi	15.7	16	16.1	14.7	16.9	17.4	18.2	18.2
Beamwidth, Horizontal,	65	59	61	71	68	66	60	62

Page 3 of 6



degrees								
Beamwidth, Vertical, degrees	8.7	7.9	7.1	7.5	5.7	5.3	4.7	4.3
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	20	19	17	15	16	17	18	20
Front-to-Back Ratio at 180°, dB	29	31	29	30	29	28	29	33
Isolation, Cross Polarization, dB	28	28	28	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25	25
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	300	300	300	250	250	250	200	200

## **Electrical Specifications**

	Y3	Y3
Frequency Band, MHz	1695-2200	2490-2690
RF Port	9-16	9-16
Gain at Mid Tilt, dBi	15.7	16.8
Beamwidth, Horizontal, degrees	101	77
Beamwidth, Vertical, degrees	5.3	4
Beam Tilt, degrees	2-12	2-12
USLS (First Lobe), dB	18	22
Front-to-Back Ratio at 180°, dB	32	31
Coupling level, Amp, Antenna port to Cal port, dB	-26	-26
Coupling level, max Amp $\Delta$ , Antenna port to Cal port, dB	±2	±2
Coupler, max Amp Δ, Antenna port to Cal port, dB	0.9	0.9
Coupler, max Phase Δ, Antenna port to Cal port, degrees	7	7
Isolation, Cross Polarization, dB	25	25
Isolation, Inter-band, dB	22	22
Isolation, Co-polarization, dB	20	20



 VSWR | Return loss, dB
 1.5 | 14.0
 1.5 | 14.0

 PIM, 3rd Order, 2 x 20 W, dBc
 -140
 -140

 Input Power per Port at 50°C, maximum, watts
 150
 150

## Electrical Specifications, Service Beam

Frequency Band, MHz	1695-2200	2490-2690
Steered 30° Gain, dBi	20.4	21
Steered 30° Beamwidth, Horizontal, degrees	31	22
Steered 30° Front-to-Back Total Power at 180° ± 30°, dB	30	28
Steered 30° Horizontal	11	9

### Electrical Specifications, Soft Split

Frequency Band, MHz	1695-2200
Gain, dBi	20
Beamwidth, Horizontal, degrees	37
Front-to-Back Total Power at 180° ± 30°, dB	30
Horizontal Sidelobe, dB	20

## **Electrical Specifications**

	Y3	Y3
Frequency Band, MHz	1695-2200	2490-2690
RF Port	9&11, 10&12, 13&15, 14&16	9&11, 10&12, 13&15, 14&16
Gain at Mid Tilt, dBi	17.3	18.4
Beamwidth, Horizontal, degrees	65	57
Beamwidth, Vertical, degrees	5.2	3.9
Beam Tilt, degrees	2-12	2-12
USLS (First Lobe), dB	20	22
Front-to-Back Ratio at 180°, dB	35	36



### Mechanical Specifications

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

 Width, packed
 565 mm | 22.244 in

 Depth, packed
 318 mm | 12.52 in

 Length, packed
 2809 mm | 110.591 in

**Weight, gross** 65 kg | 143.3 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

BSAMNT-4 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M4 – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

