

# CLAMP-SERIES-HANGER-BLOCKS

---

## Base Product



## KwikClamp™ Series Hangers

### Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	KwikClamp™

### General Specifications

<b>Cables per Hanger</b>	1
<b>Color</b>	Black
<b>Hanger Type</b>	KwikClamp™ hanger

### Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel
----------------------	--------------------------------------

### Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

### Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber