


VSRDUALAL-TS-B



Adjustable Dual V-Stabilizer™ for a Tower, large leg size (8–16 in)

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 406.4 mm (16 in) | Angle 90°, 304.8 mm (12 in) | Straight or tapered legs up to 406.4 mm (16 in) OD

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

Dimensions

Height 990.6 mm | 39 in

Face Width 4.42 m | 14.5 ft

Length 2032 mm | 80 in

Mounting Diameter, maximum 406.4 mm | 16 in

Mounting Diameter, minimum 203.2 mm | 8 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity 2

Weight, net 70.76 kg | 156 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

VSRDUALAL-TS-B

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

