


# SH-CLAMP-6F4P-5B

---



Double Hanger kits for six Fiber 4-7mm and four Power cables 9-11mm, three 4-7mm and two 9-11mm holes (along side each other), double stack; includes hardware

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

<b>Cables per Hanger</b>	10
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	3-25 mm angle iron   M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	5
<b>Height</b>	40 mm   1.575 in
<b>Width</b>	43 mm   1.693 in
<b>Length</b>	220 mm   8.661 in
<b>Compatible Cable Diameter Range</b>	4-7 mm   9-11 mm
<b>Hanger Spacing, maximum</b>	1 m   3.281 ft

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Engineered plastic   Stainless steel 304
----------------------	--

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

# SH-CLAMP-6F4P-5B

---

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Five times cable weight
<b>UV Resistance, minimum with no degradation</b>	≥124 hours exposure in accelerated UV life chamber, testing duration 1344 hrs

## Packaging and Weights

<b>Height, packed</b>	15.5 cm   6.102 in
<b>Width, packed</b>	30.5 cm   12.008 in
<b>Length, packed</b>	35.5 cm   13.976 in
<b>Included</b>	Hardware
<b>Packaging quantity</b>	27
<b>Weight, gross</b>	8 kg   17.637 lb

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power