# MPT-A2C-BB-NN-500M



HELIAX® Power cable, with aluminum shield with quantity 2x16 mm2, cores, flame resistant CPR Class B2ca s1, d2, a1 rated, 500 meters

Available with different colors on demand

### **Product Classification**

Regional Availability Europe

Product Type Power cable
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

**Warranty** For more information, please consult our Product Warranty guidelines

General Specifications

**Application** Remote radio head

Cable Type Power

Conductor Type, singles Stranded

Conductors, quantity 2

Jacket Color Black

Jacket Color, singles Blue | Brown

**Dimensions** 

 Cable Length
 500.024 m | 1,640.5 ft


 Diameter Over Jacket
 13.284 mm | 0.523 in

Conductor Gauge 16 mm<sup>2</sup>

## Cross Section Drawing



# MPT-A2C-BB-NN-500M




### **Electrical Specifications**

Safety Voltage Rating

600 V

### Ordering Tree



#### Notes

- \* this size is not available for 6, 8, or 12 core cable options.
- \*\* this size is not available for 8 and 12 core cable options.

## Material Specifications



# MPT-A2C-BB-NN-500M

**Ground Wire Material** Annealed aluminum wires

**Insulation Material, singles** Flame retardant PE

Jacket Material Flame retardant PE | Low Smoke Zero Halogen (LSZH)

Outer Shield (Braid) Coverage 100 %

Outer Shield (Tape) Material AI/PET tape

### **Environmental Specifications**

**Installation temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**Operating Temperature**  $-40 \,^{\circ}\text{C to } +90 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to } +194 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$ 

**Environmental Space** Indoor/Outdoor

Jacket UV Resistance UV stabilized

### Packaging and Weights

**Cable weight** 385.018 kg/km | 258.72 lb/kft

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

