

OBSOLETE

Replaced By:

G23HDX High Capacity Sector Frame, 10.5 ft x 2.88 in OD face pipes, includes three 2.88 OD x 96 in antenna pipes

Product Type	High capacity Tower sector frame
---------------------	----------------------------------

Application	4G LTE antenna/radio mount
--------------------	----------------------------

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Patent Number	Patent pending
----------------------	----------------

Pipe, quantity	3
-----------------------	----------

Tower Taper	Non-tapered	Tapered
-------------	-------------	---------

Height 3,200.4 mm | 126 in

Face Width 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Pipe Length 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum	218.44 mm 8.6 in
-----------------------------------	--------------------


Mounting Diameter, minimum 38.1 mm | 1.5 in

Pipe Outer Diameter	60.325 mm 2.375 in
----------------------------	----------------------

Stand-off Distance 1,226.82 mm | 48.3 in

SFG23HD-10-3-126

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Frame | Pipe mounts | Plain end pipes (3) | Stiff arm | Tower attachment

Packaging quantity 1

Weight, net 346.091 kg | 763 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code