

RVV-65D-R3VB-V3



6-port sector antenna, 2x 694–960 and 4x 1695–2690 MHz, 65° HPBW, 3x RET

- All Internal RET actuators are connected in “Cascaded SRET” configuration
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Aluminum
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	4
RF Connector Quantity, low band	2
RF Connector Quantity, total	6

Remote Electrical Tilt (RET) Information


RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10–30 Vdc
Internal RET	Low band (1) Mid band (2)
Power Consumption, active state, maximum	10 W
Power Consumption, idle state, maximum	2 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

RVV-65D-R3VB-V3

Width	397 mm 15.63 in
Depth	157 mm 6.181 in
Length	2497 mm 98.307 in
Net Weight, antenna only	28 kg 61.729 lb


Array Layout



Array ID	Frequency (MHz)	RF Connector	HPBW	RET (SRET)	AISG No.	AISG RET UID
R1	694-960	1 - 2	65°	1	AISG1	CPxxxxxxxxxxxxR1
Y1	1695-2690	3 - 4	65°	2	AISG1	CPxxxxxxxxxxxxY1
Y2	1695-2690	5 - 6	65°	3	AISG1	CPxxxxxxxxxxxxY2

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



RVV-65D-R3VB-V3

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	900 W

Electrical Specifications

	R1	R1	R1	Y1,Y2	Y1,Y2	Y1,Y2	Y1,Y2
Frequency Band, MHz	698–806	790–894	890–960	1695–1995	1920–2300	2300–2500	2490–2690
RF Port	1,2	1,2	1,2	3-6	3-6	3-6	3-6
Gain, dBi	16.6	17.1	17.3	17.5	18.2	18.5	18.6
Beamwidth, Horizontal, degrees	65	62	60	62	62	57	56
Beamwidth, Vertical, degrees	8.6	7.8	7.3	6.1	5.5	5	4.8
Beam Tilt, degrees	2–12	2–12	2–12	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	19	19	18	17	20	21	20
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	30	32	31	30	29	29	29
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28	28
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	250	250	250	200	200	200	200

Electrical Specifications, BASTA

	698–806	790–894	890–960	1695–1995	1920–2300	2300–2500	2490–2690
Frequency Band, MHz	698–806	790–894	890–960	1695–1995	1920–2300	2300–2500	2490–2690
Gain by all Beam Tilts, average, dBi	16.4	16.9	17.1	17.2	17.7	18.1	18.4
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.3	±0.3	±0.7	±0.6	±0.5	±0.3
Beamwidth, Horizontal Tolerance, degrees	±2	±2	±2	±4	±4	±3	±3
Beamwidth, Vertical Tolerance, degrees	±0.4	±0.5	±0.2	±0.5	±0.5	±0.3	±0.2
CPR at Boresight, dB	24	25	25	22	24	25	24

RVV-65D-R3VB-V3

Mechanical Specifications

Wind Loading @ Velocity, frontal	669.0 N @ 150 km/h (150.4 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	399.0 N @ 150 km/h (89.7 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	1,080.0 N @ 150 km/h (242.8 lbf @ 150 km/h)
Wind Speed, maximum	200 km/h (124 mph)

Packaging and Weights

Width, packed	492 mm 19.37 in
Depth, packed	277 mm 10.906 in
Length, packed	2697 mm 106.181 in
Weight, gross	40.4 kg 89.067 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
UK-ROHS	Compliant

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	-----------------------------------------------------------------