

FDH3000-MINI-CABINET

Base Product



Mini FDH 3000, Small Cabinet

- Miniaturized cabinet takes up less space on poles and walls
- The same Mini Fiber Distribution Hub will serve both indoor and outdoor applications
- Carefully designed fiber paths reduce attenuation and signal loss

CommScope's Mini FDH (19"H x 13"W x 8"D) is our smallest outdoor cabinet to date! This splice/MPO/HMFOC cabinet was designed to address the unique density requirements found in multi-dwelling units (MDUs) and outdoor rural fiber deployments. With a maximum of eight feeder fibers, 72 distribution fibers, and 4 standard plug-and-play splitter slots available, our smallest FDH cabinet provides network flexibility for developing architectures.

Offering quick and easy technician access to subscriber connections, the same Mini FDH can serve both indoor or outdoor applications for both wall or pole mount installation.

Key Features:

- Up to 72f of distribution
- Same PNP splitter as standard FDH3000, 4 splitter slots
- All-front access
- Pole or Wall mount
- Splice, MPO, or HMFOC configurable
- Parking lot fiber storage
- Technician-friendly; easy installation and easy fiber and connector access
- Intuitive cable routing allowing bend radius protection
- Sealed cabinet protects fibers from dust, rain, insects and other contaminants

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Warranty	One year

General Specifications

Access	Front
Color	Putty white
Mounting	Pole Wall
Splitter Slots, quantity	4

Material Specifications

Finish	Powder coated
---------------	---------------

FDH3000-MINI-CABINET

Material Type Aluminum

Environmental Specifications

Environmental Space Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE | Telcordia GR-487-CORE

Packaging and Weights

Packaging quantity 1

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines