

NG4-VXLFG08AAN



NG4 Module, CEx 5, 8 circuits, LC/APC connectors

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin America | North America

Product Type

Coexistence Element (CEx)

Product Series

NG4

Government Funding

Build America Buy America (BABA) compliant*

General Specifications

Circuits, quantity

8

Interface, Input

LC/APC

Interface, Output

LC/APC

Location of Manufacturing


Waived per BABA waiver for BEAD Program

Port Configuration

NG4-VXLFG08AAN

Module Type	Networks/Services	Wavelengths (nm)
CEx 1	GPON/25G	1290 - 1500
	UPG	1260-1280 & 1525-1650
CEx 2	GPON/25G	1290 - 1500
	XGS-PON UPG	1260 - 1280; 1575 - 1581 1525-1560 & 1596-1650
CEx 3	GPON/25G	1290 - 1500
	RF UPG	1550 - 1560 1260-1280 & 1525-1540 & 1575-1650
CEx 4	GPON/25G	1290 - 1500
	XGS-PON	1260 - 1280 & 1575 - 1581
	NG-PON2	1524-1544 & 1596-1603
CEx 5	PON (COMBI)	1260-1500nm & 1575-1581nm
	UPG	1525-1565nm & 1596-1650nm

Block Diagram



Optical Specifications

Directivity, minimum	50 dB
Input Power, maximum	200 mW
Passband	PON (COMBI): 1260-1500 nm & 1575-1581 nm UPG: 1525-1565 nm & 1596-1650 nm
Polarization Dependent Loss, maximum	0.3 dB
Polarization Mode Dispersion, maximum	0.5 ps
Insertion Loss, including connectors	COM to PON: ≤ 0.8 dB COM to UPG: ≤ 0.6 dB

NG4-VXLFG08AAN

Isolation	COM to PON: ≥ 30 dB COM to UPG: ≥ 15 dB
Return Loss, minimum	50 dB

Environmental Specifications

Operating Temperature	-10 °C to +65 °C (+14 °F to +149 °F)
Relative Humidity	5%–95%, non-condensing
Qualification Standards	Telcordia GR-63

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

