



Fiber indoor cable, Low Smoke Zero Halogen Indoor Distribution, 4 fiber single-unit, singlemode, G.657.A1, Meters jacket marking, Yellow jacket color

## Product Classification

<b>Regional Availability</b>	China
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor cable
<b>Product Series</b>	L-DS
<b>Country Specific for</b>	China

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Jacket Color</b>	Yellow
<b>Jacket Marking</b>	Meters
<b>Strength Members</b>	E-glass yarns
<b>Total Fiber Count</b>	4

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	0.9 mm   0.035 in
<b>Diameter Over Jacket</b>	5 mm   0.197 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	100 mm   3.937 in
<b>Minimum Bend Radius, unloaded</b>	50 mm   1.969 in
<b>Tensile Load, long and short term</b>	See Sag and Tension tables in Product Documentation section
<b>Tensile Load, long term, maximum</b>	198 N   44.512 lbf
<b>Tensile Load, short term, maximum</b>	660 N   148.374 lbf
<b>Cable Crush Resistance, maximum</b>	10 N/mm   57.101 lb/in

# 760255307 | L-004-DS-8Z-MSUYL/09X/B2

<b>Compression</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1 E3   IEC 60794-1-2 E3
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-2-E1

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1
-------------------	----------------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	0.3 dB/km @ 1,550 nm   0.3 dB/km @ 1,625 nm   0.40 dB/km @ 1,310 nm
-----------------------------	---

## Environmental Specifications

<b>Installation temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Cable Qualification Standards</b>	Telcordia GR-409
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)   Low Smoke Zero Halogen (LSZH)
<b>Flame Test Listing</b>	B2
<b>Flame Test Method</b>	GB/T 31247

## Environmental Test Specifications

<b>Temperature Cycle</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1 F1   IEC 60794-1-2 F1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

# 760255307 | L-004-DS-8Z-MSUYL/09X/B2

---

CS-8Z-TB-0.40/0.30/093 – Low Water Peak, Dispersion-Unshifted Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable