# SFG23RHDXL-15-B



G23RHDXL PIM OPTIMIZED SPACING High Capacity Sector Frame with extended 10' Spine for RRU Mounting & extended frame for sites requiring increased sector to sector antenna spacing. 27/8in OD x 15ft face. Antenna pipes sold separately.

### Product Classification

Product Type	High capacity Tower sector frame
Product Brand	PIM-guard
Product Series	G2

#### **General Specifications**

Mounting	Angle 60°, 203.2 mm (8 in)   Straight or tapered legs up to 203.2 mm (8 in) OD	
Patent Number	For patents see: www.cs-pat.com	
Pipe, quantity	0	
Sectors, quantity	1	
Tower Taper	Non-tapered   Tapered	

#### Dimensions

Height	838.2 mm   33 in
Face Width	4.572 m   15 ft
Width	4,572 mm   180 in
Face Support Pipe Diameter	73.025 mm   2.875 in
Mounting Diameter, maximum	203.2 mm   8 in
Mounting Diameter, minimum	38.1 mm   1.5 in
Pipe Outer Diameter	73.025 mm   2.875 in
Stand-off Distance	1,549.4 mm   61 in

#### Material Specifications

**Material Type** 

Hot dip galvanized steel

TIA/EIA-222-G

#### Mechanical Specifications

Wind Rating

Wind Rating Test Method

For Specifications, please contact your local ANDREW representative

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners.

## SFG23RHDXL-15-B

#### Packaging and Weights

IncludedFrame | Stiff arms (2) | Tower attachmentPackaging quantity1

## \* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025