# 760003939 | 0-008-CA-8W-F08NS



Fiber OSP cable, TeraSPEED® Single Jacket/Single Armor, Gel-Filled, 8 fibers, Outdoor Central Tube, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series O-CA

### General Specifications

Armor Type Corrugated steel

Cable Type Central loose tube

Construction Type Armored
Subunit Type Gel-filled
Jacket Color Black
Jacket Marking Feet
Subunit, quantity 1
Fibers per Subunit, quantity 8

#### **Dimensions**


**Total Fiber Count** 

Buffer Tube/Subunit Diameter4 mm | 0.157 inDiameter Over Jacket11 mm | 0.433 in

# Representative Image



#### 760003939 0-008-CA-8W-F08NS



## Material Specifications

**Compression Test Method** 

**Jacket Material** ΡF

## Mechanical Specifications

Minimum Bend Radius, loaded 165 mm | 6.496 in Minimum Bend Radius, unloaded 110 mm | 4.331 in Tensile Load, long term, maximum 800 N | 179.847 lbf Tensile Load, short term, maximum 2700 N | 606.984 lbf Compression 44 N/mm | 251.246 lb/in FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

**Impact Test Method** FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

**Twist** 10 cycles

**Twist Test Method** FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 607 m | 1,991.47 ft

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1, TeraSPEED® | OS2



# 760003939 | 0-008-CA-8W-F08NS

## **Environmental Specifications**

Installation temperature

-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | EN 187105

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

Heat Age Test Method IEC 60794-1 F9

**Low High Bend** -30 °C to +60 °C (-22 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 135 kg/km | 90.716 lb/kft

# Regulatory Compliance/Certifications

Compliant

# AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant



UK-ROHS



# 760003939 | 0-008-CA-8W-F08NS

#### Included Products

CS-8W-LT

 TeraSPEED® G652D/G657A1 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



# TeraSPEED®

#### TeraSPEED® G652D/G657A1 Singlemode Fiber

#### Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance**  $\pm 0.7 \, \mu m$ 0.7 % Cladding Non-Circularity, maximum **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm Core/Clad Offset, maximum  $0.5 \, \mu m$ 

**Proof Test** 689.476 N/mm<sup>2</sup> | 100000 psi

**Dimensions** 

**Fiber Curl, minimum** 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 | 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

**COMMSCOPE®** 

# CS-8W-LT

## **Optical Specifications**

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

**Attenuation, typical** 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

**Backscatter Coefficient** -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

1,385 nm

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sqrt(km)

Standards Compliance IEC 60793-2-10, edition 6, model A1a.4 | ITU-T G.652.

D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

# **Environmental Specifications**

Heat Aging, maximum 0.05 dB/km @ 85 °C

Temperature Dependence, maximum0.05 dB/kmTemperature Humidity Cycling, maximum0.05 dB/km

**Water Immersion, maximum** 0.05 dB/km @ 23 °C

## Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

COMMSCOPE®

# CS-8W-LT

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F) **Temperature Dependence, maximum** 

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

