760255051 | PPL-SP-16LC-SM-RPT-BEU

Propel Singlemode Splice Cassette, 16LC/UPC with internal shutters, OS2 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 4 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia	Australia/New Zealand	EMEA	Latin America	North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Ribbon pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	16

Dimensions

Height	67.31 mm	2.65 in
Width	131.013 mm	5.158 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

Qualification Standards	IEC 61753-1	TIA-568.3-D
Safety Standard	UL

COMMSCOPE®

Packaging and Weights

Included   Single Fusion Splice Protection Sleeves

Packaging quantity   1

Included Products

FST-ACC006   –   Mass Fusion Splice Protector (See Specs for packaging size and MOQ)

COMMSCOPE®

FST-ACC006

Mass Fusion Splice Protector (See Specs for packaging size and MOQ)

Product Classification

Regional Availability	North America
Product Type	Fiber protection sleeve
Ordering Note	Minimum order quantity (MOQ) is 5 pieces

General Specifications

Splicing Type	Heat shrink, mass fusion

Environmental Specifications

Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Packaging quantity	5

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

COMMSCOPE®