

HCA-A01A



Fiber Optic Drop Cable Assembly, PRODIGY™ Connector Core to Stub, SST Dielectric Cable

- Cable assembly with the Prodigy™ small form hardened connector
- Compact and small footprint, space-saving design for high-density environments
- Compatible with multiple hardened connectors

Product Classification

Regional Availability	Latin America North America
Product Type	Fiber drop cable assembly
Product Brand	PRODIGY™
Product Series	HCA

General Specifications


Cable Type	Dielectric - Flat
Connector A, quantity	1
Color, boot A	Black
Color, connector A	Black
Interface, Connector A	Prodigy®
Interface, Connector B	Unterminated
Jacket Color	Black
Total Fibers, quantity	1

Dimensions


Cable Assembly Length Range (ft)	1 – 2000
Cable Outer Diameter	4.5 x 8.0 mm (0.18 x 0.31 in)

Outline Drawing

HCA-A01A



Ordering Tree



*Additional connector options available upon request. Pulling sock included with non hardened connectors 25lbs of pulling force.
 **Drops are automatically coiled 0 to 1000 ft unless "L" or "R" is specified for the range of length. Drops are automatically spooled at 1,001ft with connector B deploying first from spool. Add "L" to lengths over 1,001ft if Connector A needs to deploy first.
 ***Cable length shown as an example; additional cable lengths available upon request up to 2,500

Mechanical Specifications

Minimum Bend Radius, loaded	90 mm 3.543 in
Minimum Bend Radius, unloaded	81 mm 3.189 in
Tensile Load, long term, maximum	400 N 89.924 lbf

HCA-A01A

Tensile Load, short term, maximum	1334 N 299.895 lbf
Cable Crush Resistance, maximum	10 N/mm 57.101 lb/in
Dust Cap Pulling Force, minimum	445 N 100.04 lbf
Mating Durability, maximum	0.5 dB @ 100 cycles

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2/B2
Insertion Loss, maximum, connector A	0.4 dB
Insertion Loss, typical	0.15 dB
Return Loss, minimum, connector A	65 dB

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Outdoor
Jacket UV Resistance	UV stabilized
Qualification Standards	Telcordia GR-3120-CORE

Packaging and Weights

Cable weight	39 kg/km 26.207 lb/kft
---------------------	--------------------------