
# FT-24CGAHBN



#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Product Type	Wireless Fiber Cable Assemblies	
Product Series	FT	
Ordering Note	ANDREW® Standard Product in Europe	
General Specifications		
Construction Type	Discrete fiber trunk	
Interface, Connector A	HMFOC	
Interface Feature, connector A	Uniboot	
Interface Body Style, connector A	Straight	
Interface, Connector B	LC/APC	
Interface Feature, connector B	Uniboot	
Interface Body Style, connector B	Straight	
Jacket Color	Black	
Total Fibers, quantity	24	
Dimensions		
Cable Assembly Length Range (m)	5 - 150	
Diameter Over Jacket	8.9 mm   0.35 in	
Mechanical Specifications		
Minimum Bend Radius, furcation	30 mm   1.181 in	
Minimum Bend Radius, loaded	178 mm   7.008 in	
Minimum Bend Radius, unloaded	89 mm   3.504 in	
Optical Specifications		
Fiber Mode	Singlemode	

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## FT-24CGAHBN

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

### **Environmental Specifications**

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Indoor   Outdoor

#### \* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

